



H-WASH[®] SS

Hand Sanitisation Station

All-in-one unit, for hand sanitisation anywhere

Manufactured from 70% recycled durable material, these sturdy units are ideal for a wide range of industries and applications. The unit holds 1x 5 litre hand gel container, tissue or wipes, a waste bin and storage of 1x 5 litre hand gel refill. Ideal for spaces where soap and water is not convenient.

Lockable dispenser holds 5L hand sanitiser container, and connects directly to the neck of the container.

Brand the units with your company logo.

Easy to clean - with removeable drip plate

Compact 300x300mm footprint - overall dimensions of: 300x1530x300mm (wxhxd).



Robust design, comes fully assembled with 12x units to a pallet.

Paper-tissue or antibacterial wipes dispenser included.

Integrated waste bin, which is emptied from the back of the unit.

Storage for extra 5L container

Weight: 33 lbs

Dimensions: 11.8 X 60 X 11.8 inch (WxHxD)



Set-up Instructions for H-WASH SS

Please ensure that you read these instructions and follow every step to create your H-WASH SS hand-wash station.



Step 1

Unpack your unit and ensure that it is placed on stable ground. Fix through the base if necessary to secure the unit to the ground.



Step 4

Remove the drip tray and insert your centrefeed roll of paper towel or wipes into the area below.



Step 2

Unscrew the cap off your 5L hand sanitiser container and replace with the dispenser nozzle.



Step 5

Remove the bin and pull out the removable shelf from the front of the unit. Place your spare 5L hand sanitiser container into the base of the unit and replace the shelf and bin.



Step 3

Remove the top of the unit and place the 5L container with fitted nozzle into the unit with the container upside down, and nozzle pointing towards the floor. Replace the top of the unit.



Step 6

Carry out a daily cleaning routine on the unit, using Anti-bacterial cleaning spray.

